



Representative Image

## Catalog No. TC342A

**Description:** 2WAY ADH MTG BASE 1.1X1.1IN NAT NYL

**UPC No** 786210823133

**Home > Wire & Cable Management > Ty-Rap > Cable tie mounts**

Two-Way Mounting Base, Natural Nylon 6.6 for Temperatures up to 65 Degrees Celsius (149 F), Length of 28.6mm (1.13 Inches), Width of 28.6mm (1.13 Inches), Height of 6.4mm (0.25 Inches), Self-Adhesive Mounting Method, Bulk Pack

### Descriptors

Category	Cable tie mounts
Special Features	One-piece molding - no lost parts

### Specifications

Material	Nylon/Polyamide 6.6
Color	Natural
Mounting	Self-Adhesive
Operating Temperature	up to 149 F

### Classifications

Brand Name	Ty-Rap
------------	--------

### Compliance and Certifications

RoHS	RoHS3 Compliant
REACH	REACH 247 Compliant
TSCA	TSCA Section 6(h) Compliant

ETIM	EC000449 Mounting base and -element for cable ties
Length	28.9 mm
Length	1.13 inch
Width	28.6 mm
Width	1.13 inch
Height	6.4 mm
Height	0.25 inch
Type of fastening	Self-adhesive
Material	Plastic
Material quality	Polyamide (PA)
Colour	Natural colour


**by ABB**

**Certification/Standard**

<b>CLASS</b>	<b>File Number</b>	<b>Class</b>	<b>CCN</b>	<b>Certificate Number</b>	<b>Library Number</b>
UL	E49405	N/A	N/A	N/A	N/A