



Representative Image

Catalog No. TCC5-G

Description: PVC CTD SPLIT CPLG 1-1/2IN IRON GRY

UPC No 704508411817

Home > Cable Protection Systems > Ocal > Electrical conduit coupling

PVC Double Coated Split Coupling, 1-1/2 Inch/41 Metric Pipe Size, Nominal .002 Inch (2 Mil) Blue Urethane on Both Interior and Exterior, Minimum .040 Inch (40 Mil) PVC Bonded To Exterior, Malleable Iron, Gray

Descriptors

Category	Electrical conduit coupling
Special Features	Stainless Steel Hardware Included
Application	To Join Threaded Conduit Where a Standard Coupling Cannot Be Used

Specifications

Material	Iron
Color	Gray

Classifications

Brand Name	Ocal
------------	------

Dimensions

Trade Size	1-1/2 in , 41 mm
------------	------------------

Compliance and Certifications

RoHS	RoHS3 Compliant
REACH	REACH 247 Compliant
TSCA	TSCA Section 6(h) Compliant

ETIM	EC000939 Coupler for installation tubes
Material	Metal
Material quality	Other
Surface protection	Other
For nominal tube diameter	41 mm
Two piece	N
With inspection opening and cover	N


by ABB