



Representative Image

## Catalog No. TDT3321

**Description: 30A 3P DBL THR N1 240V FUSIBLE**

**UPC No 783164069273**

**Home > Switches & Disconnects > Disconnect & Safety Switches > Safety Switches > Double Throw**

When it comes to getting the job done right, you can count on safety switches from ABB. ABB offers a wide variety of general duty switches for residential and light commercial purposes, while the extensive line of heavy-duty switches is best suited for commercial and industrial applications. For the toughest industrial environments — such as cement foundries, steel mills and processing plants — dust-tight and stainless steel switches are available. We also offer a variety of double throw switches for emergency generators. No matter the application, we've got you covered with a rugged, reliable and easy-to-install Spec-Setter safety switch. 30A 3P DBL THR N1 240V FUSIBLE

### Descriptors

|             |              |
|-------------|--------------|
| Category    | Double Throw |
| GO Schedule | SB           |

### Specifications

|                           |                 |
|---------------------------|-----------------|
| Voltage                   | 240 AC          |
| Amperage                  | 30 A            |
| Poles                     | 3               |
| Wires                     | 3               |
| Fusing                    | Fusible         |
| Enclosure                 | NEMA 1 (Indoor) |
| Options                   | None            |
| Wire Range (Cu/Al)        | 14-2 (Cu/Al)    |
| 240 Vac, Time Delay, 1-ph | 3 hp            |
| 240 Vac, Time Delay, 3-ph | 7.5 hp          |
| 480 Vac, Time Delay, 1-ph | 7.5 hp          |
| 480 Vac, Time Delay, 3-ph | 15 hp           |
| 600 Vac, Time Delay, 1-ph | 10 hp           |
| 600 Vac, Time Delay, 3-ph | 20 hp           |
| 250 Vdc                   | 5 hp            |
| GSA Compliance            | No              |

### Classifications

|            |     |
|------------|-----|
| cUL Listed | Yes |
| UL Listed  | Yes |

### Dimensions

|        |          |
|--------|----------|
| Height | 37.00 in |
| Depth  | 9.88 in  |
| Width  | 12.75 in |

## Dimensions

Weight

47 lb