



Representative Image

Catalog No. TDT3362

Description: 60A 3P DBL THR N1 600V FUSIBLE

UPC No 783164069457

Home > Switches & Disconnects > Disconnect & Safety Switches > Safety Switches > Double Throw

When it comes to getting the job done right, you can count on safety switches from ABB. ABB offers a wide variety of general duty switches for residential and light commercial purposes, while the extensive line of heavy-duty switches is best suited for commercial and industrial applications. For the toughest industrial environments — such as cement foundries, steel mills and processing plants — dust-tight and stainless steel switches are available. We also offer a variety of double throw switches for emergency generators. No matter the application, we've got you covered with a rugged, reliable and easy-to-install Spec-Setter safety switch. 60A 3P DBL THR N1 600V FUSIBLE

Descriptors

| | |
|-------------|--------------|
| Category | Double Throw |
| GO Schedule | SB |

Specifications

| | |
|---------------------------|-----------------|
| Voltage | 600 AC |
| Amperage | 60 A |
| Poles | 3 |
| Wires | 3 |
| Fusing | Fusible |
| Enclosure | NEMA 1 (Indoor) |
| Options | None |
| Wire Range (Cu/Al) | 14-2 (Cu/Al) |
| 240 Vac, NEC Std, 1-ph | 3 hp |
| 240 Vac, NEC Std, 3-ph | 7.5 hp |
| 240 Vac, Time Delay, 1-ph | 10 hp |
| 240 Vac, Time Delay, 3-ph | 15 hp |
| 480 Vac, NEC Std, 3-ph | 15 hp |
| 480 Vac, Time Delay, 1-ph | 20 hp |
| 480 Vac, Time Delay, 3-ph | 30 hp |
| 600 Vac, NEC Std, 1-ph | 10 hp |
| 600 Vac, NEC Std, 3-ph | 15 hp |
| 600 Vac, Time Delay, 1-ph | 25 hp |
| 600 Vac, Time Delay, 3-ph | 50 hp |
| 125 Vdc | 5 hp |
| 250 Vdc | 10 hp |
| GSA Compliance | No |

Classifications

| | |
|------------|-----|
| cUL Listed | Yes |
| UL Listed | Yes |

by ABB

Dimensions

| | |
|--------|----------|
| Height | 37.00 in |
| Width | 12.00 in |
| Weight | 43 lb |