

Representative Image

Catalog No. TE100CS

Description: ENCLOSURE NEMA 4/4X 100A

UPC No 783164040999

Home > Circuit Breakers > Circuit Breaker Enclosures

Designed for commercial and industrial applications where safety, high performance and continuity of service are essential. Listed to UL standard 98 enclosed and dead front switches. Suitable for use as service equipment when installed in accordance with the National Electrical Code. Certified to CSA standard 22.2 no. 4-04 enclosed and dead front switches. Meets or exceeds NEMA KS1 standard for enclosed switches, type HD. Fusible and non-fusible switches available (consult BuyLog for interrupt ratings). Quick-make, quick-break mechanism. 60/75 C conductor rating. Full cover interlocks. TE100CS

Descriptors

Category	Circuit Breaker Enclosures
GO Schedule	B2

Specifications

Enclosure Type	NEMA Type 4/4X
Mounting	Surface
Frame Type	E150
Amperage	100 A
Material	Stainless Steel
GSA Compliance	No

Classifications

UL/CUL Listing	UL

Dimensions

Height	19.25 in
Width	8.50 in
Weight	14.29 lb

by ABB