



Representative Image

Catalog No. TEB111040

Description: 1 POLE 120VAC 125VDC 40A BREAKER

UPC No 783164104073

Home > Circuit Breakers > Molded Case Circuit Breakers > Thermal Magnetic

The E150 product line consists of Thermal Magnetic Circuit Breakers, Magnetic Circuit Breakers, and Molded-Case Switches rated up to 150 Amps and 600 Volts AC. Catalog numbers include the complete breaker or switch. The WL catalog number suffix indicates that the devices come with Cu/Al line and load lugs. 1 POLE 120VAC 125VDC 40A BREAKER

Descriptors

| | |
|--------------|------------------|
| Category | Thermal Magnetic |
| Product Line | Thermal Magnetic |
| GO Schedule | EB |

Specifications

| | |
|-----------------------------|---------------------------|
| Trip Style | Non-Interchangeable |
| Poles | 1 |
| Amperage | 40 A |
| System Voltage | 120 Vac 125 Vdc |
| Frame Type | E150 |
| 120 Vac Interrupting Rating | 10 KAIC |
| 125 Vdc Interrupting Rating | 5 KAIC |
| Trip Function | LI |
| Continuous Current Rated | Standard |
| Suitable for Reverse Feed | Yes |
| Lugs | TC041 TCAL12 TCAL14 |
| Long Time | Fixed |
| Instantaneous | Fixed |
| Current Metering | No |
| Protective Relays | No |
| Special Markings | HACR |
| GSA Compliance | No |

Classifications

| | |
|-----------|---------|
| UL File # | E11592 |
| CSA File# | LR57114 |