

Representative Image

## Catalog No. TEB122015

**Description: TEB 2 POLE 240V 10K IC 15 AMP**

**UPC No 783164068504**

**Home > Circuit Breakers > Molded Case Circuit Breakers > Thermal Magnetic**

The E150 product line consists of Thermal Magnetic Circuit Breakers, Magnetic Circuit Breakers, and Molded-Case Switches rated up to 150 Amps and 600 Volts AC. Catalog numbers include the complete breaker or switch. The WL catalog number suffix indicates that the devices come with Cu/Al line and load lugs. All TEB, TED, THED breakers suitable for reverse feed. 60/75 C rating through 100 amperes, 75 C rating above 100 amperes. TEB 2 POLE 240V 10K IC 15 AMP

### Descriptors

| | |
|---|---|
| Category | Thermal Magnetic |
| GO Schedule | EB |

### Specifications

| | |
|---|---|
| Poles | 2 |
| Amperage | 15 A |
| Frame Type | E150 |
| Trip Function | LI |
| GSA Compliance | No |

## Publications

| Title | Publication No. | Publication Type |
| --- | --- | --- |
| Submittal Drawing,TEB122015 Breaker,Modular Metering<br>Submittal Drawing,TEB122015 Breaker,Modular Metering | DEE-826 | Drawings-Outline and Dimensional |

**Additional Documentation:** Visit our Publication Library to find technical documentation, time current curves, CSI Specifications and promotional literature.