



**Catalog No. TEB122020**

**Description: TEB 2 POLE 240V 10K IC 20 AMP**

**UPC No 783164068528**

**Home > Circuit Breakers > Molded Case Circuit Breakers > Thermal Magnetic**

The E150 product line consists of Thermal Magnetic Circuit Breakers, Magnetic Circuit Breakers, and Molded-Case Switches rated up to 150 Amps and 600 Volts AC. Catalog numbers include the complete breaker or switch. The WL catalog number suffix indicates that the devices come with Cu/Al line and load lugs. All TEB, TED, THED breakers suitable for reverse feed. 60/75 C rating through 100 amperes, 75 C rating above 100 amperes. TEB 2 POLE 240V 10K IC 20 AMP

**Descriptors**

Category	Thermal Magnetic
GO Schedule	EB

**Specifications**

Poles	2
Amperage	20 A
Frame Type	E150
Trip Function	LI
GSA Compliance	No

## Publications

Title	Publication No.	Publication Type
<a href="#">Submittal Drawing,TEB122020 Breaker,Modular Metering</a>	DEE-827	Drawings-Outline and Dimensional
Submittal Drawing,TEB122020 Breaker,Modular Metering		

**Additional Documentation:** Visit our Publication Library to find technical documentation, time current curves, CSI Specifications and promotional literature.