

Representative Image

Catalog No. TEB122Y100

Description: CIRCUIT BREAKER NON AUTO

UPC No 783164067644

Home > Circuit Breakers > Molded Case Circuit Breakers > Thermal Magnetic

The E150 product line consists of Thermal Magnetic Circuit Breakers, Magnetic Circuit Breakers, and Molded-Case Switches rated up to 150 Amps and 600 Volts AC. Catalog numbers include the complete breaker or switch. The WL catalog number suffix indicates that the devices come with Cu/Al line and load lugs. CIRCUIT BREAKER NON AUTO

Descriptors

Category	Thermal Magnetic
Product Line	Thermal Magnetic
GO Schedule	EB

Specifications

Poles	2
Amperage	100 A
System Voltage	120 Vac 120/240 Vac 125 Vdc 240 Vac 250 Vdc
Frame Type	E150
Trip Function	Switch
Continuous Current Rated	Standard
Suitable for Reverse Feed	Yes
Lugs	TC041 TCAL15
Long Time	No
Current Metering	No
Protective Relays	No
GSA Compliance	No

Classifications

UL File #	E11592
CSA File#	LR57114