



**Catalog No. TEB132015**

**Description: 3 POLE 240VAC 15A BREAKER**

**UPC No 783164068788**

**Home > Circuit Breakers > Molded Case Circuit Breakers > Thermal Magnetic**

The E150 product line consists of Thermal Magnetic Circuit Breakers, Magnetic Circuit Breakers, and Molded-Case Switches rated up to 150 Amps and 600 Volts AC. Catalog numbers include the complete breaker or switch. The WL catalog number suffix indicates that the devices come with Cu/Al line and load lugs. All TEB, TED, THED breakers suitable for reverse feed. 60/75 C rating through 100 amperes, 75 C rating above 100 amperes. 3 POLE 240VAC 15A BREAKER

**Descriptors**

Category	Thermal Magnetic
GO Schedule	EB

**Specifications**

Poles	3
Amperage	15 A
Frame Type	E150
Trip Function	LI
GSA Compliance	No

## Publications

Title	Publication No.	Publication Type
<a href="#">15A 3PH TEB BREAKER 10K @ 208Y/120 FOR USE WITH 225A GE METER STACKS</a> TEB132015 - 3P 15A 10K Breaker for 225A Sockets Outline Drawing	DEE-839	Drawings-Outline and Dimensional

**Additional Documentation:** Visit our Publication Library to find technical documentation, time current curves, CSI Specifications and promotional literature.