

Representative Image

Catalog No. TEB132050

Description: TEB 3 POLE 240V 10K IC 50 AMP

UPC No 783164068924

Home > Circuit Breakers > Molded Case Circuit Breakers > Thermal Magnetic

The E150 product line consists of Thermal Magnetic Circuit Breakers, Magnetic Circuit Breakers, and Molded-Case Switches rated up to 150 Amps and 600 Volts AC. Catalog numbers include the complete breaker or switch. The WL catalog number suffix indicates that the devices come with Cu/Al line and load lugs. All TEB, TED, THED breakers suitable for reverse feed. 60/75 C rating through 100 amperes, 75 C rating above 100 amperes. TEB 3 POLE 240V 10K IC 50 AMP

Descriptors

Category	Thermal Magnetic
GO Schedule	EB

Specifications

Poles	3
Amperage	50 A
Frame Type	E150
Trip Function	LI
GSA Compliance	No