

Representative Image

## Catalog No. TEB132070WL

**Description: INDUSTRIAL CIRCUIT BREAKER**

**UPC No 783164068979**

**Home > Circuit Breakers > Molded Case Circuit Breakers > Thermal Magnetic**

The E150 product line consists of Thermal Magnetic Circuit Breakers, Magnetic Circuit Breakers, and Molded-Case Switches rated up to 150 Amps and 600 Volts AC. Catalog numbers include the complete breaker or switch. The WL catalog number suffix indicates that the devices come with Cu/Al line and load lugs.
INDUSTRIAL CIRCUIT BREAKER

### Descriptors

| | |
|---|---|
| Category | Thermal Magnetic |
| Product Line | Thermal Magnetic |
| GO Schedule | EB |

### Specifications

| | |
|---|---|
| Trip Style | Non-Interchangeable |
| Poles | 3 |
| Amperage | 70 A |
| System Voltage | 120 Vac<br>120/240 Vac<br>240 Vac |
| Frame Type | E150 |
| 120 Vac Interrupting Rating | 10 KAIC |
| 120/240 Vac Interrupting Rating | 10 KAIC |
| 240 Vac Interrupting Rating | 10 KAIC |
| Trip Function | LI |
| Continuous Current Rated | Standard |
| Suitable for Reverse Feed | Yes |
| Lugs | TC041<br>TCAL12A |
| Long Time | Fixed |
| Instantaneous | Fixed |
| Current Metering | No |
| Protective Relays | No |
| Special Markings | HACR |
| GSA Compliance | No |

### Classifications

| | |
|---|---|
| UL File # | E11592 |
| CSA File# | LR57114 |

by ABB