



Representative Image

Catalog No. TEB132Y100

Description: TEB 3 POLE 240V 10K IC 100NA MC SWT

UPC No 783164067651

Home > Circuit Breakers > Molded Case Circuit Breakers > Thermal Magnetic

The E150 product line consists of Thermal Magnetic Circuit Breakers, Magnetic Circuit Breakers, and Molded-Case Switches rated up to 150 Amps and 600 Volts AC. Catalog numbers include the complete breaker or switch. The WL catalog number suffix indicates that the devices come with Cu/Al line and load lugs. TEB 3 POLE 240V 10K IC 100NA MC SWT

Descriptors

| | |
|--------------|------------------|
| Category | Thermal Magnetic |
| Product Line | Thermal Magnetic |
| GO Schedule | EB |

Specifications

| | |
|---------------------------|-----------------------------------|
| Poles | 3 |
| Amperage | 100 A |
| System Voltage | 120 Vac 120/240 Vac 240 Vac |
| Frame Type | E150 |
| Trip Function | Switch |
| Continuous Current Rated | Standard |
| Suitable for Reverse Feed | Yes |
| Lugs | TC041 TCAL15 |
| Long Time | No |
| Current Metering | No |
| Protective Relays | No |
| GSA Compliance | No |

Classifications

| | |
|-----------|---------|
| UL File # | E11592 |
| CSA File# | LR57114 |