

Representative Image

Catalog No. TEB132Y100

Description: TEB 3 POLE 240V 10K IC 100NA MC SWT

UPC No 783164067651

Home > Circuit Breakers > Molded Case Circuit Breakers > Thermal Magnetic

The E150 product line consists of Thermal Magnetic Circuit Breakers, Magnetic Circuit Breakers, and Molded-Case Switches rated up to 150 Amps and 600 Volts AC. Catalog numbers include the complete breaker or switch. The WL catalog number suffix indicates that the devices come with Cu/Al line and load lugs. TEB 3 POLE 240V 10K IC 100NA MC SWT

Descriptors

Category	Thermal Magnetic
Product Line	Thermal Magnetic
GO Schedule	EB

Specifications

Poles	3
Amperage	100 A
System Voltage	120 Vac 120/240 Vac 240 Vac
Frame Type	E150
Trip Function	Switch
Continuous Current Rated	Standard
Suitable for Reverse Feed	Yes
Lugs	TC041 TCAL15
Long Time	No
Current Metering	No
Protective Relays	No
GSA Compliance	No

Classifications

UL File #	E11592
CSA File#	LR57114

by ABB