

Representative Image

Catalog No. TED134015WL

Description: 3 POLE 480VAC 15A BREAKER

UPC No 783164063011

Home > Circuit Breakers > Molded Case Circuit Breakers > Thermal Magnetic

The E150 product line consists of Thermal Magnetic Circuit Breakers, Magnetic Circuit Breakers, and Molded-Case Switches rated up to 150 Amps and 600 Volts AC. Catalog numbers include the complete breaker or switch. The WL catalog number suffix indicates that the devices come with Cu/Al line and load lugs. 3 POLE 480VAC 15A BREAKER

Descriptors

Category	Thermal Magnetic
Product Line	Thermal Magnetic
GO Schedule	EB

Specifications

Trip Style	Non-Interchangeable
Poles	3
Amperage	15 A
System Voltage	120 Vac 120/240 Vac 125 Vdc 240 Vac 250 Vdc 277 Vac 480 Vac
Frame Type	E150
120 Vac Interrupting Rating	18 KAIC
120/240 Vac Interrupting Rating	18 KAIC
125 Vdc Interrupting Rating	10 KAIC
240 Vac Interrupting Rating	18 KAIC
250 Vdc Interrupting Rating	10 KAIC
277 Vac Interrupting Rating	18 KAIC
480 Vac Interrupting Rating	18 KAIC
500 Vdc Interrupting Rating	10 KAIC
600 Vac Interrupting Rating	14 KAIC
Trip Function	LI
Continuous Current Rated	Standard
Suitable for Reverse Feed	Yes
Lugs	TC041 TCAL14
Long Time	Fixed
Instantaneous	Fixed
Current Metering	No
Protective Relays	No
Special Markings	HACR

Specifications

GSA Compliance	Yes

Classifications

UL File #	E11592
CSA File#	LR57114