

Representative Image

Catalog No. TED134100

Description: 3 POLE 480VAC 100A BREAKER

UPC No 783164063929

Home > Circuit Breakers > Molded Case Circuit Breakers > Thermal Magnetic

Designed for commercial and industrial applications where safety, high performance and continuity of service are essential. Listed to UL standard 98 enclosed and dead front switches. Suitable for use as service equipment when installed in accordance with the National Electrical Code. Certified to CSA standard 22.2 no. 4-04 enclosed and dead front switches. Meets or exceeds NEMA KS1 standard for enclosed switches, type HD. Fusible and non-fusible switches available (consult BuyLog for interrupt ratings). Quick-make, quick-break mechanism. 60/75 C conductor rating. Full cover interlocks. 3 POLE 480VAC 100A BREAKER

Descriptors

Category	Thermal Magnetic
GO Schedule	EB

Specifications

Poles	3
Amperage	100 A
Frame Type	E150
Trip Function	LI
GSA Compliance	No