

Representative Image

## Catalog No. TEDL36015

**Description: TEDL 3 POLE 600V 15 AMP**

**UPC No 783164236965**

**Home > Circuit Breakers > Molded Case Circuit Breakers > Thermal Magnetic**

Molded Case Industrial Circuit Breaker, 15-150 Amp Circuit Breakers, Thermal-Magnetic Trip, E150 Line Circuit Breakers, Types TEB, TED, THED, Noninterchangeable Trip, Add-on Current Limiter, UL Listed 100 kAIC at 480 and 600 VAC. For use with 3 Pole TED/THED only. All TEB, TED, THED breakers suitable for reverse feed. 60/75 C rating through 100 amperes, 75 C rating above 100 amperes. TEDL 3 POLE 600V 15 AMP

### Descriptors

| | |
|---|---|
| Category | Thermal Magnetic |
| GO Schedule | EB |

### Specifications

| | |
|---|---|
| Amperage | 15 A |
| GSA Compliance | No |