



Catalog No. TEDL36020

Description: TEDL 3 POLE 600V 20 AMP

UPC No 783164236972

Home > Circuit Breakers > Molded Case Circuit Breakers > Thermal Magnetic

Molded Case Industrial Circuit Breaker, 15-150 Amp Circuit Breakers, Thermal-Magnetic Trip, E150 Line Circuit Breakers, Types TEB, TED, THED, Noninterchangeable Trip, Add-on Current Limiter, UL Listed 100 kAIC at 480 and 600 VAC. For use with 3 Pole TED/THED only. All TEB, TED, THED breakers suitable for reverse feed. 60/75 C rating through 100 amperes, 75 C rating above 100 amperes. TEDL 3 POLE 600V 20 AMP

Descriptors

Category	Thermal Magnetic
GO Schedule	EB

Specifications

Amperage	20 A
GSA Compliance	No