

Representative Image

# Catalog No. TEY130

**Description: TEY 1 POLE 30 AMP**

**UPC No 783164180930**

**Home > Circuit Breakers > Molded Case Circuit Breakers > Lighting Panel Circuit Breakers**

The TEY is a one-inch wide per pole, compact, "bolt-on" circuit breaker for use on grounded 480Y/277 Vac systems. The bolt-on mounting base accessory makes the TEY suitable for varied applications as a lug-lug breaker. All TEY circuit breakers feature Quick-make / Quick-break mechanisms, common trip bars, and easy to spot trip indication to ensure safety and reliability. TEY breakers are available in 1, 2, and 3 pole versions and can be ordered with auxiliary contact and shunt trip accessories. TEY 1 POLE 30 AMP

## Descriptors

| | |
|---|---|
| Category | Lighting Panel Circuit Breakers |
| Product Line | TEY / Q-Line (Bolt-On) |
| GO Schedule | EY |

## Specifications

| | |
|---|---|
| Trip Style | Non-Interchangeable |
| Poles | 1 |
| Amperage | 30 A |
| System Voltage | 120 Vac<br>120/240 Vac<br>240 Vac<br>277 Vac |
| 120 Vac Interrupting Rating | 65 KAIC |
| 120/240 Vac Interrupting Rating | 14 KAIC |
| 240 Vac Interrupting Rating | 14 KAIC |
| 277 Vac Interrupting Rating | 14 KAIC |
| Trip Function | LI |
| Continuous Current Rated | Standard |
| Suitable for Reverse Feed | Yes |
| Long Time | Fixed |
| Instantaneous | Fixed |
| Current Metering | No |
| Protective Relays | No |
| Special Markings | HACR<br>HID |
| Wire Range (Cu/Al) | #14-2/0 |
| GSA Compliance | Yes |

## Classifications

| | |
|---|---|
| UL File # | E11592 |
| CSA File# | LR57114 |

by ABB