

Representative Image

Catalog No. TEYD3050B

Description: TEYX CIRCUIT BREAKER 3P 50A

UPC No 783164461787

Home > Circuit Breakers > Molded Case Circuit Breakers > Lighting Panel Circuit Breakers

The TEY is a one-inch wide per pole, compact, "bolt-on" circuit breaker for use on grounded 480Y/277 Vac systems. The bolt-on mounting base accessory makes the TEY suitable for varied applications as a lug-lug breaker. All TEY circuit breakers feature Quick-make / Quick-break mechanisms, common trip bars, and easy to spot trip indication to ensure safety and reliability. TEYD breakers are available in 1, 2, and 3 pole versions 2&3 pole versions can be ordered with auxiliary contact, shunt trip, undervoltage release, or bell alarm accessories. TEYx Circuit Breaker 3P 50A

Descriptors

Category	Lighting Panel Circuit Breakers
Product Line	TEY / Q-Line (Bolt-On)
GO Schedule	EY

Specifications

Trip Style	Yes
Poles	3
Amperage	50 A
System Voltage	120/240 Vac 240 Vac 250 Vdc 277 Vac 480/277 Vac
Frame Type	TEYD
120/240 Vac Interrupting Rating	65 KAIC
240 Vac Interrupting Rating	65 KAIC
480/277 Vac Interrupting Rating	25 KAIC
Trip Function	LI
Continuous Current Rated	Standard
Suitable for Reverse Feed	Yes
Long Time	Fixed
Instantaneous	Fixed
Current Metering	No
Protective Relays	No
Wire Range (Cu/Al)	#10-#4
GSA Compliance	No

Classifications

UL File #	E11592