



Representative Image

Catalog No. TEYF330

Description: TEYF 3 POLE 30 AMP

UPC No 783164388503

Home > Circuit Breakers > Molded Case Circuit Breakers > Lighting Panel Circuit Breakers

The TEYF is a one-inch wide per pole, compact, "bolt-on" circuit breaker for use on grounded 480Y/277 Vac systems. The bolt-on mounting base accessory makes the TEYF suitable for varied applications as a lug-lug breaker. All TEYF circuit breakers feature Quick-make / Quick-break mechanisms, common trip bars, and easy to spot trip indication to ensure safety and reliability. TEYF breakers are available in 1, 2, and 3 pole versions and can be ordered with auxiliary contact and shunt trip accessories. TEYF 3 POLE 30 AMP

Descriptors

| | |
|--------------|---------------------------------|
| Category | Lighting Panel Circuit Breakers |
| Product Line | TEY / Q-Line (Bolt-On) |
| GO Schedule | EY |

Specifications

| | |
|---------------------------------|--|
| Trip Style | Non-Interchangeable |
| Poles | 3 |
| Amperage | 30 A |
| System Voltage | 120/240 Vac 240 Vac 277 Vac 480/277 Vac |
| Frame Type | TEYF |
| 120/240 Vac Interrupting Rating | 65 KAIC |
| 240 Vac Interrupting Rating | 65 KAIC |
| 277 Vac Interrupting Rating | 18 KAIC |
| 480/277 Vac Interrupting Rating | 18 KAIC |
| Trip Function | LI |
| Continuous Current Rated | Standard |
| Suitable for Reverse Feed | Yes |
| Long Time | Fixed |
| Instantaneous | Fixed |
| Current Metering | No |
| Protective Relays | No |
| Special Markings | HACR |
| Wire Range (Cu/Al) | #14-#10 |
| GSA Compliance | No |

Classifications

| | |
|-----------|---------|
| UL File # | E11592 |
| CSA File# | LR57114 |