

Representative Image

## Catalog No. TEYH1050B

**Description: 50A 1POLE 35KA 480/277 CKT BKR**

**UPC No 783164461930**

**Home > Circuit Breakers > Molded Case Circuit Breakers > Lighting Panel Circuit Breakers**

The TEY is a one-inch wide per pole, compact, "bolt-on" circuit breaker for use on grounded 480Y/277 Vac systems. The bolt-on mounting base accessory makes the TEY suitable for varied applications as a lug-lug breaker. All TEY circuit breakers feature Quick-make / Quick-break mechanisms, common trip bars, and easy to spot trip indication to ensure safety and reliability. TEYH breakers are available in 1, 2, and 3 pole versions, 2&3 pole versions can be ordered with auxiliary contact, shunt trip, undervoltage release, or bell alarm accessories. 50A 1POLE 35KA 480/277 CKT BKR

### Descriptors

| | |
|---|---|
| Category | Lighting Panel Circuit Breakers |
| Product Line | TEY / Q-Line (Bolt-On) |
| GO Schedule | EY |

### Specifications

| | |
|---|---|
| Trip Style | Yes |
| Poles | 1 |
| Amperage | 50 A |
| System Voltage | 120 Vac<br>120/240 Vac<br>125 Vdc<br>240 Vac<br>277 Vac<br>480/277 Vac |
| Frame Type | TEYH |
| 120 Vac Interrupting Rating | 65 KAIC |
| 120/240 Vac Interrupting Rating | 65 KAIC |
| 277 Vac Interrupting Rating | 35 KAIC |
| Trip Function | LI |
| Continuous Current Rated | Standard |
| Suitable for Reverse Feed | Yes |
| Long Time | Fixed |
| Instantaneous | Fixed |
| Current Metering | No |
| Protective Relays | No |
| Wire Range (Cu/Al) | #10-#4 |
| GSA Compliance | No |

### Classifications

| | |
|---|---|
| UL File # | E11592 |

by ABB