

## Catalog No. TEYL1035B

**Description:** 35A 1POLE 65KA 480/277 CKT BKR

**UPC No** 783164462302

**Home > Circuit Breakers > Molded Case Circuit Breakers > Lighting Panel Circuit Breakers**

The TEY is a one-inch wide per pole, compact, "bolt-on" circuit breaker for use on grounded 480Y/277 Vac systems. The bolt-on mounting base accessory makes the TEY suitable for varied applications as a lug-lug breaker. All TEY circuit breakers feature Quick-make / Quick-break mechanisms, common trip bars, and easy to spot trip indication to ensure safety and reliability. TEYL breakers are available in 1, 2, and 3 pole versions, 2&3 pole versions can be ordered with auxiliary contact, shunt trip, undervoltage release, or bell alarm accessories. 35A 1POLE 65KA 480/277 CKT BKR



Representative Image

### Descriptors

Category	Lighting Panel Circuit Breakers
Product Line	TEY / Q-Line (Bolt-On)
GO Schedule	EY

### Specifications

Trip Style	Yes
Poles	1
Amperage	35 A
System Voltage	120 Vac 120/240 Vac 125 Vdc 240 Vac 277 Vac 480/277 Vac
Frame Type	TEYL
120 Vac Interrupting Rating	100 KAIC
120/240 Vac Interrupting Rating	100 KAIC
125 Vdc Interrupting Rating	15 KAIC
277 Vac Interrupting Rating	65 KAIC
Trip Function	LI
Continuous Current Rated	Standard
Suitable for Reverse Feed	Yes
Long Time	Fixed
Instantaneous	Fixed
Current Metering	No
Protective Relays	No
Wire Range (Cu/Al)	#10-#4
GSA Compliance	No

### Classifications

UL File #	E11592
-----------	--------