

Catalog No. TEYL3020B

Description: 20A 3POLE 65KA 480/277 CKT BKR

UPC No 783164462524

Home > Circuit Breakers > Molded Case Circuit Breakers > Lighting Panel Circuit Breakers

The TEY is a one-inch wide per pole, compact, "bolt-on" circuit breaker for use on grounded 480Y/277 Vac systems. The bolt-on mounting base accessory makes the TEY suitable for varied applications as a lug-lug breaker. All TEY circuit breakers feature Quick-make / Quick-break mechanisms, common trip bars, and easy to spot trip indication to ensure safety and reliability. TEYL breakers are available in 1, 2, and 3 pole versions 2&3 pole versions can be ordered with auxiliary contact, shunt trip, undervoltage release, or bell alarm accessories. 20A 3POLE 65KA 480/277 CKT BKR



Representative Image

Descriptors

| | |
|--------------|---------------------------------|
| Category | Lighting Panel Circuit Breakers |
| Product Line | TEY / Q-Line (Bolt-On) |
| GO Schedule | EY |

Specifications

| | |
|---------------------------------|---|
| Trip Style | Yes |
| Poles | 3 |
| Amperage | 20 A |
| System Voltage | 120/240 Vac 240 Vac 250 Vdc 277 Vac 480/277 Vac |
| Frame Type | TEYL |
| 120/240 Vac Interrupting Rating | 100 KAIC |
| 125 Vdc Interrupting Rating | 42 KAIC |
| 240 Vac Interrupting Rating | 100 KAIC |
| 250 Vdc Interrupting Rating | 35 KAIC |
| 480/277 Vac Interrupting Rating | 65 KAIC |
| Trip Function | LI |
| Continuous Current Rated | Standard |
| Suitable for Reverse Feed | Yes |
| Long Time | Fixed |
| Instantaneous | Fixed |
| Current Metering | No |
| Protective Relays | No |
| Wire Range (Cu/Al) | #14-#10 |
| GSA Compliance | No |

Classifications

| | |
|-----------|--------|
| UL File # | E11592 |
|-----------|--------|