



Representative Image

## Catalog No. TEYL3080B

**Description: TEYX CIRCUIT BREAKER 3P 80A**

**UPC No 783164462616**

**Home > Circuit Breakers > Molded Case Circuit Breakers > Lighting Panel Circuit Breakers**

The TEY is a one-inch wide per pole, compact, "bolt-on" circuit breaker for use on grounded 480Y/277 Vac systems. The bolt-on mounting base accessory makes the TEY suitable for varied applications as a lug-lug breaker. All TEY circuit breakers feature Quick-make / Quick-break mechanisms, common trip bars, and easy to spot trip indication to ensure safety and reliability. TEYL breakers are available in 1, 2, and 3 pole versions, 2&3 pole versions can be ordered with auxiliary contact, shunt trip, undervoltage release, or bell alarm accessories. TEYX CIRCUIT BREAKER 3P 80A

### Descriptors

Category	Lighting Panel Circuit Breakers
Product Line	TEY / Q-Line (Bolt-On)
GO Schedule	EY

### Specifications

Trip Style	Yes
Poles	3
Amperage	80 A
System Voltage	120/240 Vac 240 Vac 250 Vdc 277 Vac 480/277 Vac
Frame Type	TEYL
120/240 Vac Interrupting Rating	100 KAIC
125 Vdc Interrupting Rating	42 KAIC
240 Vac Interrupting Rating	100 KAIC
250 Vdc Interrupting Rating	35 KAIC
480/277 Vac Interrupting Rating	65 KAIC
Trip Function	LI
Continuous Current Rated	Standard
Suitable for Reverse Feed	Yes
Long Time	Fixed
Instantaneous	Fixed
Current Metering	No
Protective Relays	No
Wire Range (Cu/Al)	#4-2/0
GSA Compliance	No

### Classifications

UL File #	E11592
-----------	--------