



Representative Image

## Catalog No. TH3363J

**Description: 100A 3P HD N5/12 600V FUSIBLE SW**

**UPC No 783164087093**

**Home > Switches & Disconnects > Disconnect & Safety Switches > Safety Switches > Heavy Duty**

When it comes to getting the job done right, you can count on safety switches from ABB. ABB offers a wide variety of general duty switches for residential and light commercial purposes, while the extensive line of heavy-duty switches is best suited for commercial and industrial applications. For the toughest industrial environments — such as cement foundries, steel mills and processing plants — dust-tight and stainless steel switches are available. We also offer a variety of double throw switches for emergency generators. No matter the application, we've got you covered with a rugged, reliable and easy-to-install Spec-Setter safety switch. 100A 3P HD N5/12 600V FUSIBLE SW

### Descriptors

|             |            |
|-------------|------------|
| Category    | Heavy Duty |
| GO Schedule | S1         |

### Specifications

|                           |                            |
|---------------------------|----------------------------|
| Voltage                   | 600 AC                     |
| Amperage                  | 100 A                      |
| Poles                     | 3                          |
| Wires                     | 3                          |
| Fusing                    | Fusible                    |
| Enclosure                 | NEMA 5, 12 Drip/Dust-tight |
| Options                   | None                       |
| Wire Range (Cu/Al)        | 10-1/0                     |
| 480 Vac, NEC Std, 1-ph    | 10 hp                      |
| 480 Vac, NEC Std, 3-ph    | 25 hp                      |
| 480 Vac, Time Delay, 1-ph | 30 hp                      |
| 480 Vac, Time Delay, 3-ph | 60 hp                      |
| 600 Vac, NEC Std, 1-ph    | 15 hp                      |
| 600 Vac, NEC Std, 3-ph    | 30 hp                      |
| 600 Vac, Time Delay, 1-ph | 40 hp                      |
| 600 Vac, Time Delay, 3-ph | 75 hp                      |
| 250 Vdc                   | 20 hp                      |
| GSA Compliance            | Yes                        |

### Classifications

|            |     |
|------------|-----|
| cUL Listed | Yes |
| UL Listed  | Yes |

### Dimensions

|        |          |
|--------|----------|
| Height | 25.40 in |
|--------|----------|


**by ABB**

## Dimensions

|        |          |
|--------|----------|
| Depth  | 5.00 in  |
| Width  | 13.40 in |
| Weight | 36 lb    |