



Representative Image

Catalog No. TH3363J

Description: 100A 3P HD N5/12 600V FUSIBLE SW

UPC No 783164087093

Home > Switches & Disconnects > Disconnect & Safety Switches > Safety Switches > Heavy Duty

When it comes to getting the job done right, you can count on safety switches from ABB. ABB offers a wide variety of general duty switches for residential and light commercial purposes, while the extensive line of heavy-duty switches is best suited for commercial and industrial applications. For the toughest industrial environments — such as cement foundries, steel mills and processing plants — dust-tight and stainless steel switches are available. We also offer a variety of double throw switches for emergency generators. No matter the application, we've got you covered with a rugged, reliable and easy-to-install Spec-Setter safety switch. 100A 3P HD N5/12 600V FUSIBLE SW

Descriptors

Category	Heavy Duty
GO Schedule	S1

Specifications

Voltage	600 AC
Amperage	100 A
Poles	3
Wires	3
Fusing	Fusible
Enclosure	NEMA 5, 12 Drip/Dust-tight
Options	None
Wire Range (Cu/Al)	10-1/0
480 Vac, NEC Std, 1-ph	10 hp
480 Vac, NEC Std, 3-ph	25 hp
480 Vac, Time Delay, 1-ph	30 hp
480 Vac, Time Delay, 3-ph	60 hp
600 Vac, NEC Std, 1-ph	15 hp
600 Vac, NEC Std, 3-ph	30 hp
600 Vac, Time Delay, 1-ph	40 hp
600 Vac, Time Delay, 3-ph	75 hp
250 Vdc	20 hp
GSA Compliance	Yes

Classifications

cUL Listed	Yes
UL Listed	Yes

Dimensions

Height	25.40 in
--------	----------

by ABB

Dimensions

Width	13.40 in
Weight	36 lb