

Representative Image

Catalog No. THED113015WL

Description: THED 1 POLE 277V 15 AMP - WL

UPC No 783164236934

Home > Circuit Breakers > Molded Case Circuit Breakers > Thermal Magnetic

Thermal-Magnetic Trip. E150 Line Circuit Breakers. Noninterchangeable Trip. Includes Cu/Al load lugs only. If line lugs are required, add suffix (WL÷ to Product Number. UL listed for HID (high intensity discharge). All TEB, TED, THED breakers UL listed as HACR type except 10 ampere. All TEB, TED, THED breakers suitable for reverse feed. 60/75 C rating through 100 amperes, 75 C rating above 100 amperes. THED 1 POLE 277V 15 AMP - WL

Descriptors

Category	Thermal Magnetic
GO Schedule	EB

Specifications

Poles	1
Amperage	15 A
GSA Compliance	No