



Catalog No. THED113020

Description: THED 1 POLE 277V 65K IC 20 AMP

UPC No 783164138672

Home > Circuit Breakers > Molded Case Circuit Breakers > Thermal Magnetic

Industrial Circuit Breakers, Single Pole, 15-150A Circuit Breakers, Thermal-Magnetic Trip, E150 Line Circuit Breakers, THED, Noninterchangeable Trip, Single Pole Includes Cu/Al Load Lugs Only. If Line Lugs Are Required, Add Suffix WL to Product Number. All TEB, TED, THED breakers suitable for reverse feed. 60/75 C rating through 100 amperes, 75 C rating above 100 amperes. THED 1 POLE 277V 65K IC 20 AMP

Descriptors

Category	Thermal Magnetic
GO Schedule	EB

Specifications

Poles	1
Amperage	20 A
GSA Compliance	No