

Art. Nr. THED124015
Omschrijving: THED 2 POLE 480V 25K IC 15 AMP
UPC No 783164231229
Startpagina > Vermogensschakelaars > Molded Case Circuit Breakers > Thermal Magnetic

The E150 product line consists of Thermal Magnetic Circuit Breakers, Magnetic Circuit Breakers, and Molded-Case Switches rated up to 150 Amps and 600 Volts AC. Catalog numbers include the complete breaker or switch. The WL catalog number suffix indicates that the devices come with Cu/Al line and load lugs. All TEB, TED, THED breakers suitable for reverse feed. 60/75 C rating through 100 amperes, 75 C rating above 100 amperes. THED 2 POLE 480V 25K IC 15 AMP



Representatief beeld

Omschrijvingen

Category	Thermal Magnetic
GO Schedule	EB

Specificaties

Poles	2
Amperage	15 A
Frame Type	E150
Trip Function	LI
GSA Compliance	No