

Catalog No. THHQC1125WL

Description: THQB C E

UPC No 783164117813

Home > Circuit Breakers > Miniature Circuit Breakers > Q-Line Miniature Circuit Breakers

Q line circuit breakers are one-inch wide per pole, compact, thermal-magnetic devices designed for residential and commercial applications. The QC breakers are lug-lug versions of the Q Line and are available for 35mm DIN rail mounting. All Q Line circuit breakers feature Quick-make / Quick-break mechanisms, common trip bars, and easy to spot trip indication to ensure safety and reliability. Q Line breakers are available in 1, 2, and 3 pole versions and can be ordered with auxiliary contact and shunt trip accessories. 25WL Amps 25 A

Descriptors

Category	Q-Line Miniature Circuit Breakers
Product Line	Q-Line (Lug-Lug)
GO Schedule	EB

Specifications

Trip Style	Non-Interchangeable
Frame Type	Q-Line
Amperage	25 A
System Voltage	120 Vac 120/240 Vac
Poles	1
Trip Function	LI
Continuous Current Rated	Standard
120 Vac Interrupting Rating	22 KAIC
120/240 Vac Interrupting Rating	22 KAIC
Suitable for Reverse Feed	Yes
Long Time	Fixed
Instantaneous	Fixed
Protective Relays	No
Current Metering	No
Special Markings	HACR
GSA Compliance	No

Classifications

UL File #	E11592