



## Catalog No. THHQC2120LL

**Description: 2 POLE 120/240V 22KA 20A W/NO LUGS**

**UPC No 783164109313**

**Home > Circuit Breakers > Miniature Circuit Breakers > Q-Line Miniature Circuit Breakers**

Q line circuit breakers are one-inch wide per pole, compact, thermal-magnetic devices designed for residential and commercial applications. The QC breakers are lug-lug versions of the Q Line and are available for 35mm DIN rail mounting. All Q Line circuit breakers feature Quick-make / Quick-break mechanisms, common trip bars, and easy to spot trip indication to ensure safety and reliability. Q Line breakers are available in 1, 2, and 3 pole versions and can be ordered with auxiliary contact and shunt trip accessories. 20LL Amps 20 A

### Descriptors

Category	Q-Line Miniature Circuit Breakers
Product Line	Q-Line (Lug-Lug)
GO Schedule	EB

### Specifications

Trip Style	Non-Interchangeable
Frame Type	Q-Line
Amperage	20 A
System Voltage	120 Vac 120/240 Vac
Poles	2
Trip Function	LI
Continuous Current Rated	Standard
120 Vac Interrupting Rating	22 KAIC
120/240 Vac Interrupting Rating	22 KAIC
Suitable for Reverse Feed	Yes
Long Time	Fixed
Instantaneous	Fixed
Protective Relays	No
Current Metering	No
Special Markings	HACR
GSA Compliance	No

### Classifications

UL File #	E11592
-----------	--------