

Representative Image

Catalog No. THHQL1120DF

Description: EMCB DFCI 22KA QL 1P 120/240V 20A DF

UPC No 783164532111

Home > Circuit Breakers > Residential Circuit Breakers > Dual Function

Dual Function breakers (DFCI) combine the functions of AFCI and GFCI breakers, for even more protection for your home. The THHQ1120DF breaker features DFCI technology, one pole, an ampere rating of 20 A, a 22kAIC interrupting rating, and a voltage of 120/240V.

Descriptors

Category	Dual Function

Specifications

Interrupting Capacity Rating	22 kAIC
Voltage	120/240 V
Trip Style	Non-Interchangeable
Frame Type	Q-Line
Amperage	20 A
System Voltage	120 Vac
Poles	1
Trip Function	LI AFCI and GFCI
Continuous Current Rated	Standard
120 Vac Interrupting Rating	22 KAIC
Wire Range (Cu/Al)	#14-8 AWG
Long Time	Fixed
Protective Relays	No
Current Metering	No
Special Markings	HACR, SWD
GSA Compliance	No

Classifications

UL File #	E471742