

Catalog No. THHQL1145

Description: CIRCUIT BREAKER 1P 45A

UPC No 783164117448

Home > Circuit Breakers > Residential Circuit Breakers > Q Line

Q line circuit breakers are one-inch wide per pole, compact, thermal-magnetic devices designed for residential and commercial applications. The QL breakers are plug-in versions of the Q Line used for connection to load centers and lighting panels. All Q Line circuit breakers feature Quick-make / Quick-break mechanisms, common trip bars, and easy to spot trip indication to ensure safety and reliability. Q Line breakers are available in 1, 2, and 3 pole versions, can be ordered with auxiliary contact and shunt trip accessories, and can be ordered for use in HID applications. 1145 Amps 45 A

Representative Image

Descriptors

| | |
|--------------|------------------|
| Category | Q Line |
| Product Line | Q-Line (Plug-In) |
| GO Schedule | R5 |

Specifications

| | |
|---------------------------------|------------------------|
| Interrupting Capacity Rating | 22 kAIC |
| Voltage | 120/240 V |
| Trip Style | Non-Interchangeable |
| Frame Type | Q-Line |
| Amperage | 45 A |
| System Voltage | 120 Vac 120/240 Vac |
| Poles | 1 |
| Trip Function | LI |
| Continuous Current Rated | Standard |
| 120 Vac Interrupting Rating | 22 KAIC |
| 120/240 Vac Interrupting Rating | 22 KAIC |
| Suitable for Reverse Feed | Yes |
| Long Time | Fixed |
| Instantaneous | Fixed |
| Protective Relays | No |
| Current Metering | No |
| Special Markings | HACR |
| GSA Compliance | No |

Classifications

| | |
|-----------|--------|
| UL File # | E11592 |
|-----------|--------|

by ABB