

Catalog No. THQB1130GFT

Description: THQB MCB 30A 10KA 1P 120/240V GFT

UPC No 783164485493

Home > Circuit Breakers > Miniature Circuit Breakers > Q-Line Miniature Circuit Breakers

Q line circuit breakers are one-inch wide per pole, compact, thermal-magnetic devices designed for residential and commercial applications. The QL breakers are plug-in versions of the Q Line used for connection to load centers and lighting panels. All Q Line circuit breakers feature Quick-make / Quick-break mechanisms, common trip bars, and easy to spot trip indication to ensure safety and reliability. Q Line breakers are available in 1, 2, and 3 pole versions, can be ordered with auxiliary contact and shunt trip accessories, and can be ordered for use in HID applications. 0GFT Amps 30 A



Representative Image

Descriptors

| | |
|--------------|-----------------------------------|
| Category | Q-Line Miniature Circuit Breakers |
| Product Line | TEY / Q-Line (Bolt-On) |

Specifications

| | |
|-----------------------------|---------------------|
| Trip Style | Non-Interchangeable |
| Frame Type | Q-Line |
| Amperage | 30 A |
| System Voltage | 120 Vac |
| Poles | 1 |
| Trip Function | LIG |
| Continuous Current Rated | Standard |
| 120 Vac Interrupting Rating | 10 KAIC |
| Suitable for Reverse Feed | Yes |
| Long Time | Fixed |
| Instantaneous | Fixed |
| Ground Fault | Yes |
| Protective Relays | No |
| Current Metering | No |
| Special Markings | HACR |
| GSA Compliance | No |

Classifications

| | |
|-----------|--------|
| UL File # | E51075 |
|-----------|--------|