



**Catalog No. THQB2120GFT**

**Description: THQB MCB 20A 10KA 2P 120/240V GFT**

**UPC No 783164485554**

**Home > Circuit Breakers > Miniature Circuit Breakers > Q-Line Miniature Circuit Breakers**

Q line circuit breakers are one-inch wide per pole, compact, thermal-magnetic devices designed for residential and commercial applications. The QL breakers are plug-in versions of the Q Line used for connection to load centers and lighting panels. All Q Line circuit breakers feature Quick-make / Quick-break mechanisms, common trip bars, and easy to spot trip indication to ensure safety and reliability. Q Line breakers are available in 1, 2, and 3 pole versions, can be ordered with auxiliary contact and shunt trip accessories, and can be ordered for use in HID applications. 0GFT Amps 20 A

**Descriptors**

Category	Q-Line Miniature Circuit Breakers
Product Line	TEY / Q-Line (Bolt-On)

**Specifications**

Trip Style	Non-Interchangeable
Frame Type	Q-Line
Amperage	20 A
System Voltage	120/240 Vac
Poles	2
Trip Function	LIG
Continuous Current Rated	Standard
120/240 Vac Interrupting Rating	10 KAIC
Suitable for Reverse Feed	Yes
Long Time	Fixed
Instantaneous	Fixed
Ground Fault	Yes
Protective Relays	No
Current Metering	No
Special Markings	HACR
GSA Compliance	No

**Classifications**

UL File #	E51075
-----------	--------