



Representative Image

## Catalog No. THQB21WY15

**Description:** THQB MCB SWITCH 2P 15A

**UPC No** 783164103540

**Home > Circuit Breakers > Miniature Circuit Breakers > Q-Line Miniature Circuit Breakers**

Q line circuit breakers are one-inch wide per pole, compact, thermal-magnetic devices designed for residential and commercial applications. The QB breakers are bolt-on versions of the Q Line used for bolting to the bus connections of load centers and lighting panels. All Q Line circuit breakers feature Quick-make / Quick-break mechanisms, common trip bars, and easy to spot trip indication to ensure safety and reliability. Q Line breakers are available in 1, 2, and 3 pole versions, can be ordered with auxiliary contact and shunt trip accessories, and can be ordered for use in HID applications. WY15 Amps 15 A

### Descriptors

Category	Q-Line Miniature Circuit Breakers
Product Line	TEY / Q-Line (Bolt-On)
GO Schedule	EB

### Specifications

Trip Style	Non-Interchangeable
Frame Type	Q-Line
Amperage	15 A
System Voltage	120 Vac 120/240 Vac
Poles	2
Trip Function	LI
Continuous Current Rated	Standard
120 Vac Interrupting Rating	10 KAIC
120/240 Vac Interrupting Rating	10 KAIC
Suitable for Reverse Feed	Yes
Long Time	No
Protective Relays	No
Current Metering	No
GSA Compliance	No

### Classifications

UL File #	E11592
-----------	--------