



Image représentative

## n° de catalogue THQC2125WL

**Description:** CIRCUIT BREAKER 2P 25A 120/240V 10KA

**UPC No** 783164060010

**Accueil > Circuit Breakers > Miniature Circuit Breakers > Q-Line Miniature Circuit Breakers**

Q line circuit breakers are one-inch wide per pole, compact, thermal-magnetic devices designed for residential and commercial applications. The QC breakers are lug-lug versions of the Q Line and are available for 35mm DIN rail mounting. All Q Line circuit breakers feature Quick-make / Quick-break mechanisms, common trip bars, and easy to spot trip indication to ensure safety and reliability. Q Line breakers are available in 1, 2, and 3 pole versions and can be ordered with auxiliary contact and shunt trip accessories. 25WL Amps 25 A

### Descripteurs

|              |                                   |
|--------------|-----------------------------------|
| Catégorie    | Q-Line Miniature Circuit Breakers |
| Product Line | Q-Line (Lug-Lug)                  |
| GO Schedule  | EB                                |

### Spécifications

|                                 |                        |
|---------------------------------|------------------------|
| Trip Style                      | Non-Interchangeable    |
| Frame Type                      | Q-Line                 |
| Amperage                        | 25 A                   |
| System Voltage                  | 120 Vac<br>120/240 Vac |
| Poles                           | 2                      |
| Trip Function                   | LI                     |
| Continuous Current Rated        | Standard               |
| 120 Vac Interrupting Rating     | 10 KAIC                |
| 120/240 Vac Interrupting Rating | 10 KAIC                |
| Suitable for Reverse Feed       | Yes                    |
| Long Time                       | Fixed                  |
| Instantaneous                   | Fixed                  |
| Protective Relays               | No                     |
| Current Metering                | No                     |
| Special Markings                | HACR                   |
| GSA Compliance                  | No                     |

### Classifications

|           |        |
|-----------|--------|
| UL File # | E11592 |
|-----------|--------|