

Representative Image

Catalog No. THQL1115GFTS

Description: THQL 1P 120V 15A GFCI SHORT WIRE

UPC No 783164618235

Home > Circuit Breakers > Residential Circuit Breakers > Ground Fault

The short pigtail ground fault circuit interrupter (GFCI) breakers provide protection of receptacles located in the outdoors, in bathrooms, garages and spa areas. This applies to not only to new construction, but also to existing homes. When an electrical outlet is replaced in a location that requires ground-fault protection, the new outlet must be GFCI approved according to the NEC. All Q Line circuit breakers are one inch wide per pole, compact devices that feature: Quick-make / Quick-break mechanisms, common trip bars, and easy-to-spot trip indications to ensure safety and reliability as well as meets 2020 NEC standards. The THQL1115GFT breaker features reduced neutral wire length of 2 "", ground fault interrupting techonology, 1 pole, an ampere rating of 15 A, an interrupting rating of 10kAIC, and a voltage rating of 120/240V.

Descriptors

Category	Ground Fault
Product Line	Q-Line (Plug-In)
GO Schedule	R9

Specifications

Interrupting Capacity Rating	10 kAIC
Voltage	120/240 V
Neutral Connection	Short Pig Tail
Trip Style	Non-Interchangeable
Frame Type	Q-Line
Amperage	15 A
System Voltage	120 Vac, 120/240 Vac
Poles	1
Trip Function	LI
Continuous Current Rated	Standard
120/240 Vac Interrupting Rating	10 KAIC
Suitable for Reverse Feed	Yes
Long Time	Fixed
Instantaneous	Fixed
Ground Fault	Yes
Protective Relays	No
Current Metering	No
Special Markings	HACR, SWD

Classifications

UL File #	E11592