

Representative Image

Catalog No. THQL1120DF

Description: 20 A, 10 KA, DUAL FUNCT MCB, DFCI

UPC No 783164532098

Home > Circuit Breakers > Miniature Circuit Breakers > Q-Line Miniature Circuit Breakers

BRKR AFCI/GFCI 20A 1P 120V 10K PLUG-IN

Descriptors

Category	Q-Line Miniature Circuit Breakers

Specifications

Trip Style	Non-Interchangeable
Frame Type	Q-Line
Amperage	20
System Voltage	120 Vac
Poles	1
Trip Function	LI AFCI and GFCI
Continuous Current Rated	Standard
120 Vac Interrupting Rating	22 KAIC
Wire Range (Cu/Al)	#14-8 AWG
Long Time	Fixed
Protective Relays	No
Current Metering	No
Special Markings	HACR, SWD
GSA Compliance	No

Classifications

UL File #	E471742

by ABB