



Representative Image

## Catalog No. THQL1120HID

**Description:** CIRCUIT BREAKER 1P 20A

**UPC No** 783164160062

**Home > Circuit Breakers > Residential Circuit Breakers > Q Line**

HID breakers have been designed to handle the current and voltage spikes that result when gaseous discharge lamps, including fluorescent and HID lamps, are switched on and of. The THQL1120HID breaker features 1 pole, an ampere rating of 20 A, an interrupting rating of 10kAIC, and a voltage rating of 120/240V.

### Descriptors

Category	Q Line
Product Line	Q-Line (Plug-In)
GO Schedule	R5

### Specifications

Specialty Breakers	High Intensity Discharge
Interrupting Capacity Rating	10 kAIC
Voltage	120/240 V
Trip Style	Non-Interchangeable
Frame Type	Q-Line
Amperage	20 A
System Voltage	120 Vac 120/240 Vac
Poles	1
Trip Function	LI
Continuous Current Rated	Standard
120 Vac Interrupting Rating	10 KAIC
120/240 Vac Interrupting Rating	10 KAIC
Suitable for Reverse Feed	Yes
Long Time	Fixed
Instantaneous	Fixed
Protective Relays	No
Current Metering	No
Special Markings	HACR SWD
GSA Compliance	Yes

### Classifications

UL File #	E11592
-----------	--------