



Representative Image

Catalog No. THQL2160

Description: THQL 2 POLE 120/240V 10K IC 60 AMP

UPC No 783164048483

Home > Circuit Breakers > Miniature Circuit Breakers > Q-Line Miniature Circuit Breakers

THQL 2 POLE 120/240V 10K IC 60 AMP

Descriptors

Category	Q-Line Miniature Circuit Breakers
Product Line	Q-Line (Plug-In)
GO Schedule	R5

Specifications

Trip Style	Non-Interchangeable
Frame Type	Q-Line
Amperage	60
System Voltage	120 Vac 120/240 Vac
Poles	2
Trip Function	LI
Continuous Current Rated	Standard
120 Vac Interrupting Rating	10 KAIC
120/240 Vac Interrupting Rating	10 KAIC
Suitable for Reverse Feed	Yes
Long Time	Fixed
Instantaneous	Fixed
Protective Relays	No
Current Metering	No
Special Markings	HACR
GSA Compliance	Yes

Classifications

UL File #	E11592
-----------	--------