


Representative Image

## Catalog No. THQL21WY15

**Description: CIRCUIT BREAKER 2P 15A 120/240V 10KA WY**

**UPC No 783164161625**

**Home > Circuit Breakers > Residential Circuit Breakers > Q Line**

A Molded Case Switch Breaker Is used to protect the circuit from being overwhelmed with large amounts of current. This could result in the breaker short circuiting or overloading. The THQL21WY150 breaker features 2 poles, an ampere rating of 15 A, an interrupting rating of 10kAIC, and a voltage rating of 240 V.

### Descriptors

| | |
|---|---|
| Category | Q Line |
| Product Line | Q-Line (Plug-In) |
| GO Schedule | R5 |

### Specifications

| | |
|---|---|
| Specialty Breakers | Molded Case Switch |
| Interrupting Capacity Rating | 10 kAIC |
| Voltage | 120/240 V |
| Trip Style | Non-Interchangeable |
| Frame Type | Q-Line |
| Amperage | 15 A |
| System Voltage | 120 Vac<br>120/240 Vac |
| Poles | 2 |
| Trip Function | LI |
| Continuous Current Rated | Standard |
| 120 Vac Interrupting Rating | 10 KAIC |
| 120/240 Vac Interrupting Rating | 10 KAIC |
| Suitable for Reverse Feed | Yes |
| Long Time | No |
| Protective Relays | No |
| Current Metering | No |
| GSA Compliance | Yes |

### Classifications

| | |
|---|---|
| UL File # | E11592 |

by ABB