



Representative Image

Catalog No. THQL21WY25

Description: CIRCUIT BREAKER 2P 25A

UPC No 783164121643

Home > Circuit Breakers > Residential Circuit Breakers > Q Line

A Molded Case Switch Breaker Is used to protect the circuit from being overwhelmed with large amounts of current. This could result in the breaker short circuiting or overloading. The THQL21WY25 breaker features 2 poles, an ampere rating of 25 A, an interrupting rating of 10kAIC, and a voltage rating of 240 V.

Descriptors

Category	Q Line
Product Line	Q-Line (Plug-In)
GO Schedule	R5

Specifications

Specialty Breakers	Molded Case Switch
Interrupting Capacity Rating	10 kAIC
Voltage	120/240 V
Trip Style	Non-Interchangeable
Frame Type	Q-Line
Amperage	25 A
System Voltage	120 Vac 120/240 Vac
Poles	2
Trip Function	LI
Continuous Current Rated	Standard
120 Vac Interrupting Rating	10 KAIC
120/240 Vac Interrupting Rating	10 KAIC
Suitable for Reverse Feed	Yes
Long Time	No
Protective Relays	No
Current Metering	No
GSA Compliance	No

Classifications

UL File #	E11592
-----------	--------