

Representative Image

Catalog No. THQL21WY30

Description: CIRCUIT BREAKER 2P 30A 120/240V 10KA WY

UPC No 783164000658

Home > Circuit Breakers > Residential Circuit Breakers > Q Line

A Molded Case Switch Breaker Is used to protect the circuit from being overwhelmed with large amounts of current. This could result in the breaker short circuiting or overloading. The THQL21WY30 breaker features 2 poles, an ampere rating of 30 A, an interrupting rating of 10kAIC, and a voltage rating of 240 V.

Descriptors

Category	Q Line
Product Line	Q-Line (Plug-In)
GO Schedule	R5

Specifications

Specialty Breakers	Molded Case Switch
Interrupting Capacity Rating	10 kAIC
Voltage	120/240 V
Trip Style	Non-Interchangeable
Frame Type	Q-Line
Amperage	30 A
System Voltage	120 Vac 120/240 Vac
Poles	2
Trip Function	LI
Continuous Current Rated	Standard
120 Vac Interrupting Rating	10 KAIC
120/240 Vac Interrupting Rating	10 KAIC
Suitable for Reverse Feed	Yes
Long Time	No
Protective Relays	No
Current Metering	No
GSA Compliance	No

Classifications

UL File #	E11592