

Representative Image

Catalog No. THQL22040

Description: CIRCUIT BREAKER 2P 40A 240V 10KA

UPC No 783164012989

Home > Circuit Breakers > Residential Circuit Breakers > Q Line

Q Line circuit breakers are one-inch wide per pole, compact, thermal-magnetic devices designed for residential and commercial applications in load centers or lighting panels. All Q Line circuit breakers feature Quick-make / Quick-break mechanisms, common trip bars, and easy to spot trip indication to ensure safety and reliability. Q Line breakers can be ordered with auxiliary contact and shunt trip accessories, and can be ordered for use in HID applications. The THQL22040 breaker features 2 poles, an ampere rating of 40 A, an interrupting rating of 10kAIC, and a voltage of 240V.

Descriptors

Category	Q Line
Product Line	Q-Line (Plug-In)
GO Schedule	R8

Specifications

Interrupting Capacity Rating	10 kAIC
Voltage	240 V
Trip Style	Non-Interchangeable
Frame Type	Q-Line
Amperage	40 A
System Voltage	120 Vac 120/240 Vac 240 Vac
Poles	2
Trip Function	LI
Continuous Current Rated	Standard
120 Vac Interrupting Rating	10 KAIC
120/240 Vac Interrupting Rating	10 KAIC
240 Vac Interrupting Rating	10 KAIC
Suitable for Reverse Feed	Yes
Long Time	Fixed
Instantaneous	Fixed
Protective Relays	No
Current Metering	No
Special Markings	HACR
GSA Compliance	No

Classifications

UL File #	E11592

by ABB