

## Catalog No. THQL32020ST1

**Description: CIRCUIT BREAKER 3P 20A 240 10KA ST1**

**UPC No 783164231519**

**Home > Circuit Breakers > Residential Circuit Breakers > Q Line with Shunt Trip**

Shunt Trip breakers provide all the basic features of a standard breaker, plus they provide a connection for an external power shut off switch outside the main breaker. The THQL32020ST1 breaker features a shunt trip, 3 poles, an ampere rating of 20 A, an interrupting rating of 10kAIC, and a voltage rating of 240V.



Representative Image

### Descriptors

Category	Q Line with Shunt Trip
Product Line	Q-Line (Plug-In)
GO Schedule	R8

### Specifications

Interrupting Capacity Rating	10 kAIC
Voltage	240 V
Trip Style	Non-Interchangeable
Frame Type	Q-Line
Amperage	20 A
System Voltage	120 Vac 120/240 Vac 240 Vac
Poles	3
Trip Function	LI
Continuous Current Rated	Standard
120 Vac Interrupting Rating	10 KAIC
120/240 Vac Interrupting Rating	10 KAIC
240 Vac Interrupting Rating	10 KAIC
Suitable for Reverse Feed	Yes
Long Time	Fixed
Instantaneous	Fixed
Protective Relays	No
Current Metering	No
Special Markings	HACR
GSA Compliance	No

### Classifications

UL File #	E11592
-----------	--------