



Representative Image

Catalog No. TJK436F000

Description: TJK 3-POLE 400-AMP FRAME ONLY

UPC No 783164013764

Home > Circuit Breakers > Molded Case Circuit Breakers > Thermal Magnetic

The J600 product line consists of Thermal Magnetic Circuit Breakers, Magnetic Circuit Breakers, and Molded-Case Switches rated up to 600 Amps and 600 Volts AC. These breakers are available with either non-interchangeable trips (designated type TJJ) or interchangeable trips (designated types TJK/THJK). Type TJJ devices ship fully assembled while types TJK/THJK ship unassembled unless specified on the order. TJK breakers are available in two frames, 400 ampere frame (125 to 400 amperes) and 600 ampere frame (250 to 600 amperes). Trip units are not interchangeable between frames. The WL catalog number suffix indicates that the devices come with Cu/Al line and load lugs. TJK 3-POLE 400-AMP FRAME ONLY

Descriptors

Category	Thermal Magnetic
Product Line	Thermal Magnetic
GO Schedule	EL

Specifications

Trip Style	Interchangeable
Poles	3
Amperage	125 A 150 A 175 A 200 A 225 A 250 A 300 A 350 A 400 A
System Voltage	120 Vac 120/240 Vac 125 Vdc 240 Vac 250 Vdc 277 Vac 480 Vac 500 Vdc 600 Vac
Frame Type	J600
120 Vac Interrupting Rating	42 KAIC
120/240 Vac Interrupting Rating	42 KAIC
125 Vdc Interrupting Rating	20 KAIC
240 Vac Interrupting Rating	42 KAIC
250 Vdc Interrupting Rating	20 KAIC
277 Vac Interrupting Rating	30 KAIC
480 Vac Interrupting Rating	30 KAIC
500 Vdc Interrupting Rating	20 KAIC
600 Vac Interrupting Rating	22 KAIC
Continuous Current Rated	Standard

Specifications

Lugs	TC043 TCAL43 TCAL47
Long Time	Fixed
Instantaneous	Adjustable
Current Metering	No
Protective Relays	No
GSA Compliance	No

Classifications

UL File #	E11592
CSA File#	LR40350