



Representative Image

## Catalog No. TL240RCU

**Description: 2 CIRC 40A OUTDOOR**

**UPC No 783164275483**

**Home > Load Centers > Load Centers**

Main lug load centers can be used as a home's main panel or sub panel depending upon your preferences. All ABB load centers are rated up to 60 degree/75 degree centigrade and is suitable for use with service entrance equipment when installed in accordance with electrical code. The TL240RCU features space for 2, 1" breakers, 40 A bus ampere rating, and an outdoor suitable enclosure.

### Descriptors

Category	Load Centers
GO Schedule	RD
Grouping	Single Phase - USA

### Specifications

1" Space	2
1/2" Space	4
Amperage	40 A
Circuit Breaker Style	Plug-In
Device type	Main Lug
Door	Yes
Enclosure	Outdoor
Enclosure Type	Outdoor, Surface Mount
Factory Installed Ground Kit	No
Feed	Either
Input/Output Voltage	120/240V ac
Interrupting Capacity Rating	65
Load Center Type	Standard
NEMA Rating	NEMA 3R
Phase	1 Phase
Service & Voltage	1 Phase, 3 Wire, 120/240V ac
Wires	3 Wire

### Classifications

UL/CUL Listing	UL
----------------	----