



Representative Image

## Catalog No. TL240SCU

**Description: 2 CIRC 40A INDOOR SURFACE**

**UPC No 783164275469**

**Home > Load Centers > Load Centers**

Main lug load centers can be used as a home's main panel or sub panel depending upon your preferences. All ABB load centers are rated up to 60 degree/75 degree centigrade and is suitable for use with service entrance equipment when installed in accordance with electrical code. The TL240SCU features space for 2, 1" breakers, a 40 A bus ampere rating, and a surface enclosure.

### Descriptors

|             |                    |
|-------------|--------------------|
| Category    | Load Centers       |
| GO Schedule | RD                 |
| Grouping    | Single Phase - USA |

### Specifications

|                              |                              |
|------------------------------|------------------------------|
| 1" Space                     | 2                            |
| 1/2" Space                   | 4                            |
| Amperage                     | 40 A                         |
| Circuit Breaker Style        | Plug-In                      |
| Device type                  | Main Lug                     |
| Door                         | No                           |
| Enclosure                    | Indoor                       |
| Enclosure Type               | Indoor, Surface Mount        |
| Factory Installed Ground Kit | No                           |
| Feed                         | Either                       |
| Input/Output Voltage         | 120/240V ac                  |
| Interrupting Capacity Rating | 65                           |
| Load Center Type             | Standard                     |
| NEMA Rating                  | NEMA 1                       |
| Phase                        | 1 Phase                      |
| Service & Voltage            | 1 Phase, 3 Wire, 120/240V ac |
| Wires                        | 3 Wire                       |

### Classifications

|                |    |
|----------------|----|
| UL/CUL Listing | UL |
|----------------|----|